




## Welding thermowell for temperature sensors

THERMOWELL, D6/WELD-IN/L=230



EC 1935/2004 EHEDG Certified



| Application                    |       |                                                |
|--------------------------------|-------|------------------------------------------------|
| Design                         |       | for temperature sensors EL = 300 mm            |
| Pressure rating                | [bar] | 400                                            |
| Pressure rating                | [MPa] | 40                                             |
| Accuracy / deviations          |       |                                                |
| Max. permissible flow velocity | [m/s] | 25                                             |
| Mechanical data                |       |                                                |
| Weight                         | [g]   | 1236                                           |
| Materials                      |       | stainless steel (316L/1.4404)                  |
| Sensor connection              |       | 1/2" NPS Ø 6 mm suitable for G1/2 and 1/2" NPT |
| Process connection             |       | welding adapter Ø 38,1 mm                      |
| Installation length EL         | [mm]  | 191                                            |
| Bore length BL                 | [mm]  | 228.6                                          |
| Remarks                        |       |                                                |
| Pack quantity                  |       | 1 pcs.                                         |