


IM513A



Inductive sensor

IMC4030-CPKG/US/3D/3G



Product characteristics

Electrical design	PNP
Output function	complementary
Sensing range [mm]	30
Housing	rectangular
Dimensions [mm]	40 x 40 x 54

Application

Special feature	Gold-plated contacts
-----------------	----------------------

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 15
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	complementary
Max. voltage drop switching output DC [V]	2.5
Max. leakage current [mA]	0.1

IM513A



Inductive sensor

IMC4030-CPKG/US/3D/3G

Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	100
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone		
Sensing range	[mm]	30
Real sensing range Sr	[mm]	30 ± 10 %
Operating distance	[mm]	0...24.3

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...20
Switch point drift	[% of Sr]	-10...10

Operating conditions		
Ambient temperature	[°C]	-20...60
Protection		IP 65; IP 67

Tests / approvals		
Approval		BVS 20 ATEX E 057 X; IECEx BVS 20.0044 X
ATEX marking		II 3G Ex ec IIC T4 Gc
		II 3D Ex tc IIIC T95°C Dc
EMC		EN 60947-5-2
MTTF	[years]	1260

Mechanical data		
Weight	[g]	173
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	40 x 40 x 54
Materials		PC; PA; TPE

Displays / operating elements		
Display	switching status	1 x LED, yellow

Remarks		
Remarks		Recommendation: Check the safe functioning of the unit after a short circuit. 5 positions of the active zone possible
Pack quantity		1 pcs.

IM513A



Inductive sensor

IMC4030-CPKG/US/3D/3G

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

