

Inductive sensor

IEC2002-BROG



Product characteristics

Electrical design	PNP/NPN
Output function	normally closed
Sensing range [mm]	2
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 35

Electrical data

Operating voltage [V]	10...30 DC
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	3.5
Minimum load current [mA]	4
Max. leakage current [mA]	0.8
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	2000
Short-circuit protection	no
Overload protection	no

Detection zone

Sensing range [mm]	2
Real sensing range S_r [mm]	$2 \pm 10 \%$
Operating distance [mm]	0...1.62

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [% of Sr]	1...15
Switch point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

IE5192



Inductive sensor

IEC2002-BROG

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV DC / 8 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
MTTF	[years]	4529

Mechanical data		
Weight	[g]	38.6
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M8 x 1 / L = 35
Thread designation		M8 x 1
Materials		PBT
Tightening torque	[Nm]	0.25

Displays / operating elements		
Display	switching status	1 x LED, yellow



Accessories		
Items supplied		lock nuts: 2
		rubber washers: 2

Remarks		
Pack quantity		1 pcs.

Electrical connection		
-----------------------	--	--

Cable: 2 m, PVC; 2 x 0.14 mm²

Connection		
------------	--	--



Core colours :
BN = brown
BU = blue