


Inductive sensor

IEB32,5-BPKG/V4A/AS



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	2.5
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 50

Application

Special feature	Increased sensing range
-----------------	-------------------------

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1200
Short-circuit protection	yes
Overload protection	yes

Detection zone

Sensing range [mm]	2.5
Real sensing range S_r [mm]	$2.5 \pm 10 \%$
Operating distance [mm]	0...2.03
Increased sensing range	yes

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [% of S_r]	1...20
Switch point drift [% of S_r]	-10...10

IE5292



Inductive sensor


IEB32,5-BPKG/V4A/AS

Operating conditions		
Ambient temperature	[°C]	0...80
Protection		IP 65; IP 67; (with ifm socket duly screwed on)
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011 emission	class B
MTTF	[years]	1376
Embedded software included		yes
UL approval	Ta	0...80 °C
	Enclosure type	Type 1
	power supply	Limited Voltage/Current
	UL Approval no.	A017
	File number UL	E174191
Mechanical data		
Weight	[g]	18
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M8 x 1 / L = 50
Thread designation		M8 x 1
Materials		stainless steel (316L/1.4404); cover: LCP; LED window: PPSU; potting: oil resistant; lock nuts: stainless steel (316 / 1.4401)
Tightening torque	[Nm]	A = 5 mm: 2 Nm; B = 5 Nm
Displays / operating elements		
Display	switching status	4 LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		
Connector: 1 x M8; coding: A		

Inductive sensor

IEB32,5-BPKG/V4A/AS

Connection



Diagrams and graphs

Installation

