


# MK5111



## T-slot cylinder sensor

MKT3028BBPKG/G/0,3M/-H/US



- 1 fastening clamp  
2 Sensing face



### Product characteristics

|                   |               |
|-------------------|---------------|
| Electrical design | PNP           |
| Output function   | normally open |
| Dimensions [mm]   | 25 x 5 x 6.5  |

### Electrical data

|                               |                                         |
|-------------------------------|-----------------------------------------|
| Operating voltage [V]         | 10...30 DC; ("supply class 2" to cULus) |
| Current consumption [mA]      | < 10                                    |
| Protection class              | III                                     |
| Reverse polarity protection   | yes                                     |
| Max. power-on delay time [ms] | 30                                      |

### Outputs

|                                                      |               |
|------------------------------------------------------|---------------|
| Electrical design                                    | PNP           |
| Output function                                      | normally open |
| Max. voltage drop switching output DC [V]            | 2.5           |
| Permanent current rating of switching output DC [mA] | 100           |
| Switching frequency DC [Hz]                          | 10000         |
| Short-circuit protection                             | yes           |
| Type of short-circuit protection                     | pulsed        |
| Overload protection                                  | yes           |

### Detection zone

|                           |      |
|---------------------------|------|
| Response sensitivity [mT] | 2.8  |
| Travel speed [m/s]        | > 10 |

# MK5111



## T-slot cylinder sensor

MKT3028BBPKG/G/0,3M/-H/US

| Accuracy / deviations                                                               |                           |                                                                             |
|-------------------------------------------------------------------------------------|---------------------------|-----------------------------------------------------------------------------|
| Hysteresis                                                                          | [mm]                      | 1.5                                                                         |
| Repeatability                                                                       | [mm]                      | < 0.2                                                                       |
| Operating conditions                                                                |                           |                                                                             |
| Ambient temperature                                                                 | [°C]                      | -25...85                                                                    |
| Protection                                                                          |                           | IP 65; IP 67; IP 69K                                                        |
| Tests / approvals                                                                   |                           |                                                                             |
| EMC                                                                                 | EN 61000-4-2 ESD          | - CD / 8 kV AD                                                              |
|                                                                                     | EN 61000-4-3 HF radiated  | 10 V/m                                                                      |
|                                                                                     | EN 61000-4-4 Burst        | 2 kV                                                                        |
|                                                                                     | EN 61000-4-6 HF conducted | 10 V                                                                        |
|                                                                                     | EN 55011                  | class B                                                                     |
| MTTF                                                                                | [years]                   | 2373                                                                        |
| UL approval                                                                         | Ta                        | -25...75 °C                                                                 |
|                                                                                     | Enclosure type            | Type 1                                                                      |
|                                                                                     | power supply              | Limited Voltage/Current (Marking Class 2)                                   |
|                                                                                     | UL Approval no.           | C003                                                                        |
|                                                                                     | File number UL            | E174191                                                                     |
| Mechanical data                                                                     |                           |                                                                             |
| Weight                                                                              | [g]                       | 20.9                                                                        |
| Mounting                                                                            |                           | flush mountable                                                             |
| Type of mounting                                                                    |                           | fastening clamp with combined slot / hexagon socket, width across flats 1.5 |
| Cylinder type                                                                       |                           | T-slot cylinders                                                            |
| Dimensions                                                                          | [mm]                      | 25 x 5 x 6.5                                                                |
| Materials                                                                           |                           | housing: PA; fastening clamp: stainless steel                               |
| Displays / operating elements                                                       |                           |                                                                             |
| Display                                                                             | switching status          | 1 x LED, yellow                                                             |
| Accessories                                                                         |                           |                                                                             |
| Items supplied                                                                      |                           | rubber placeholder: 1                                                       |
|                                                                                     |                           | Cable clip: 1                                                               |
| Remarks                                                                             |                           |                                                                             |
| Pack quantity                                                                       |                           | 1 pcs.                                                                      |
| Electrical connection - plug                                                        |                           |                                                                             |
| Cable: 0.3 m, PVC                                                                   |                           |                                                                             |
| Connector: 1 x M12; coding: A; Locking: Hexagon nut, rotatable, stainless steel     |                           |                                                                             |
|  |                           |                                                                             |

# MK5111



## T-slot cylinder sensor

MKT3028BBPKG/G/0,3M/-H/US

### Connection

