




Through-beam sensor receiver

OAE-FCKG



- 1 selection switch and potentiometer under cover receiver in upper lens



Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Special feature	Function check output
Function principle	Through-beam sensor

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 50
Protection class	II
Reverse polarity protection	yes
Type of light	infrared light
Wave length [nm]	880

Outputs

Electrical design	PNP/NPN
Output function	light-on/dark-on mode; (programmable)
Function check output	yes
Max. current load for function check output [mA]	10



Through-beam sensor receiver

OAE-FCKG

Permanent current rating of switching output DC	[mA]	250
Max. current load in dual output mode	[mA]	100
Switching frequency DC	[Hz]	300
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Transmitter / receiver		receiver
Range	[m]	< 50
Range adjustable		yes

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 65

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	399

Mechanical data

Weight	[g]	281
Housing		rectangular
Dimensions	[mm]	90 x 30 x 70
Materials		PPO modified
Lens material		PMMA
Lens alignment		side lens

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red

Accessories

Items supplied	Angle bracket: 1, E20514 screwdrivers
----------------	--

Remarks

Pack quantity	1 pcs.
---------------	--------


Through-beam sensor receiver

OAE-FCKG

Electrical connection

terminals: ...1.5 mm²; Cable sheath: Ø 4.5...10 mm; Cable gland: M16 X 1.5

Connection



5 Function check output

Diagrams and graphs

excess gain graph

