


Diffuse reflection sensor with background suppression

OGWIHPKG/US/IO-LINK



1 potentiometer



Product characteristics

Type of light	infrared light
Housing	threaded type

Application

Special feature	Background suppression
Application [m]	0.025...2
Function principle	Diffuse reflection sensor

Electrical data

Operating voltage [V]	10...30 DC; ("supply class 2" to cULus)
Current consumption [mA]	< 30
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	300
Type of light	infrared light
Wave length [nm]	940

Outputs

Electrical design	PNP
Output function	light-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Short-circuit protection	yes
Type of short-circuit protection	pulsed

Detection zone

Range [mm]	25...400
Range adjustable	yes
Max. light spot diameter [mm]	200
Light spot dimensions refer to	at maximum range



Diffuse reflection sensor with background suppression

OGWIHPKG/US/IO-LINK

Background suppression available	yes	
Background suppression [m]	2	
Measuring/setting range		
Sampling rate [Hz]	10	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Smart Sensor: Device Identification; Switching Signal Channel; Process Data Variable; Device Diagnosis; Tech Channel	
SIO mode	yes	
Required master port type	A	
Min. process cycle time [ms]	10	
Supported DeviceIDs	Type of operation	DeviceID
	default	1161
Operating conditions		
Ambient temperature [°C]	-20...55	
Storage temperature [°C]	-40...85	
Protection	IP 65	
Max. immunity to extraneous light [klx]	8	
Tests / approvals		
EMC	EN 60947-5-2	
Notes on laser protection	Caution:	laser light
	laser class:	1
		EN / IEC60825-1:2007
		EN / IEC60825-1:2014
		Complies with 21 CFR 1040 except for deviations pursuant to Laser Notice No. 50, dated June 2007.
MTTF [years]	690	
UL approval	Ta	-20...55 °C
	Enclosure type	Type 1
	power supply	Class 2
	File number UL	E174191
Mechanical data		
Weight [g]	55.2	
Housing	threaded type	
Dimensions [mm]	M18 x 1 / L = 72	
Thread designation	M18 x 1	
Materials	housing: stainless steel (316L/1.4404); sensor surface: PMMA; ABS; operator interface: TPE; lock nuts: brass white bronze coated	
Lens material	PMMA	
Displays / operating elements		
Display	switching status	4 x 90° LED, yellow




Diffuse reflection sensor with background suppression

OGWIHPKG/US/IO-LINK


Operating elements	potentiometer
Accessories	
Items supplied	lock nuts: 2 x M18
Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A




Connection



4 OUT / IO-Link


Diagrams and graphs



- 1 < 8 kLux
- 2 < 3 kLux
- 3 < 1 kLux

Diffuse reflection sensor with background suppression

OGWIHPKG/US/IO-LINK



a: sensor

b: object

c: background

x: distance sensor/object [mm]

y: min. distance object/background [mm]