


PG2798



Flush pressure sensor with analogue display

PG-,25BREA01-MFRKG/US/ /P



ACS CE CRN cUL^{us} LISTED EC 1935/2004 EHEDG Certified FCM FDA Reg31 S UK CA

Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1		
Measuring range	-0.0124...0.25 bar	-12.4...250 mbar	-5...100.4 inH2O
Process connection	threaded connection G 1 external thread Aseptoflex Vario		

Application

Special feature	Gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Media	viscous media and liquids with suspended particles; liquids and gases		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	30000 mbar	12043 inH2O	
Min. bursting pressure [MPa]		3	
Pressure rating	6000 mbar	2400 inH2O	
Pressure rating [MPa]		1	
Type of pressure	relative pressure		
No dead space	yes		



Flush pressure sensor with analogue display

PG-,25BREA01-MFRKG/US/ /P

MAWP (for applications according to CRN)	[bar]	10
--	-------	----

Electrical data		
Operating voltage	[V]	18...32 DC
Current consumption	[mA]	< 70; (24 V)
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	6
Measuring principle		hydrostatic
Integrated watchdog		yes

Inputs / outputs	
Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1

Outputs		
Total number of outputs		2
Output signal		switching signal; analogue signal; (configurable)
Electrical design		PNP/NPN
Number of digital outputs		1
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	50
Number of analogue outputs		1
Analogue current output	[mA]	4...20, invertible; (scalable)
Max. load	[Ω]	(U _b - 10 V) / 20 mA
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Measuring/setting range			
Measuring range	-0.0124...0.25 bar	-12.4...250 mbar	-5...100.4 inH2O
Set point SP	-12...400 mbar		-4.8...160.6 inH2O
Reset point rP	-12.4...399.6 mbar		-5...160.4 inH2O
Analogue start point	-12.4...337.6 mbar		-5...135.5 inH2O
Analogue end point	50...400 mbar		20.1...160.6 inH2O
In steps of	0.2 mbar		0.1 inH2O

Accuracy / deviations	
Switch point accuracy	< ± 0,5; (Turn down 1:1)
[% of the span]	
Repeatability	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)
[% of the span]	
Characteristics deviation	< ± 0,5; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)
[% of the span]	
Linearity deviation	< ± 0,15; (Turn down 1:1)
[% of the span]	



Flush pressure sensor with analogue display

PG-,25BREA01-MFRKG/US/ /P

Hysteresis deviation [% of the span]	$< \pm 0,15$; (Turn down 1:1)
Long-term stability [% of the span]	$< \pm 0,1$; (Turn down 1:1; per year)
Temperature coefficient zero point [% of the span / 10 K]	$< \pm 0,05$; (0...70 °C)
Temperature coefficient span [% of the span / 10 K]	$< \pm 0,15$; (0...70 °C)

Response times

Response time [ms]	< 10
Damping process value dAP [s]	0.01...30
Damping for the analogue output dAA [s]	0.01...30
Step response time analogue output [ms]	25

Operating conditions

Ambient temperature [°C]	-25...80
Storage temperature [°C]	-40...100
Protection	IP 67; IP 69K

Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5/1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF [years]	100	
Note on approval	factory certificate available as download at www.factory-certificate.ifm	
UL approval	File number UL	E174189

Mechanical data

Weight [g]	520.75
Dimensions [mm]	153 x 100 x 57
Materials	stainless steel (316L/1.4404); PA; FKM; PTFE; viewing glass: laminated safety glass 4 mm
Materials (wetted parts)	ceramics (99.9 % Al ₂ O ₃); stainless steel (316L/1.4435); surface characteristics: Ra < 0,4 / Rz 4; PTFE
Min. pressure cycles	100 million
Process connection	threaded connection G 1 external thread Aseptoflex Vario

Displays / operating elements

Display	Display unit	2 x LED, green
	switching status	LED, yellow
	switch points	LED ring, red
	function display	alphanumeric display, red 4-digit
	measured values	analogue display, 0...350° rotatable, pointer not visible when unit disconnected
	measured values	alphanumeric display, red 4-digit

PG2798



Flush pressure sensor with analogue display

PG-,25BREA01-MFRKG/US/ /P

With scale	yes	
Extended display range (max.)	400 mbar	160.6 inH2O



Remarks		
Remarks	characteristics deviation in the extended display range: 1.5 % of the span	
	switch point accuracy in the extended display range: 1.5 % of the span	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1 switching output
OUT2 analogue output