


Inductive sensor

IIA2010RABOA/6M



Product characteristics

Electrical design	series connection possible AC 100 V = max. 2 AC 200 V = max. 4	
Output function	normally open	
Sensing range [mm]	10	
Housing	threaded type	
Dimensions [mm]	M30 x 1.5 / L = 81	

Electrical data

Operating voltage [V]	20...250 AC/DC	
Protection class	II	
Reverse polarity protection	no	

Outputs

Electrical design	series connection possible AC 100 V = max. 2 AC 200 V = max. 4	
Output function	normally open	
Max. voltage drop switching output DC [V]	7.5	
Max. voltage drop switching output AC [V]	7.5	
Minimum load current [mA]	5	
Max. leakage current [mA]	4	
Permanent current rating of switching output AC [mA]	70; (200 (...50 °C))	
Permanent current rating of switching output DC [mA]	100	
Short-time current rating of switching output [mA]	2200; (20 ms / 0,5 Hz)	
Switching frequency AC [Hz]	25	
Switching frequency DC [Hz]	50	
Short-circuit proof	no	
Overload protection	no	

Detection zone

Sensing range [mm]	10	
Real sensing range Sr [mm]	10 ± 10 %	
Operating distance [mm]	0...8.1	



Inductive sensor

IIA2010RABOA/6M

Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	3...15	
Switch point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature		[°C]	-25...80
Protection			IP 67
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
MTTF		[years]	689
Mechanical data			
Weight		[g]	412
Housing			threaded type
Mounting			flush mountable
Dimensions		[mm]	M30 x 1.5 / L = 81
Thread designation			M30 x 1.5
Materials			brass nickel-plated; PBT
Displays / operating elements			
Display		switching status	1 x LED, red
Electrical connection			
Required protection		miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting	
Accessories			
Items supplied		lock nuts: 2	
Remarks			
Remarks		Recommendation: Check the safe functioning of the unit after a short circuit.	
Pack quantity		1 pcs.	

II0310



Inductive sensor

IIA2010RABOA/6M

Electrical connection

Cable: 6 m, PVC; 2 x 0.5 mm²

Connection



Note miniature fuse to IEC60127-2 sheet 1 ≤ 2 A fast acting
Core colours :

BN =

brown

BU =

blue