

PI7094




Flush pressure sensor with display

PI-010-RES30-QFRKG/US/ /P

phase-out article
Discontinuation date: 03/31/2024

Alternative articles: PI1004 or PI1704
When selecting an alternative article and accessories please note that technical data may differ!

Please do not use for new projects.
no more adapters available as accessories



- 1 alphanumeric display 4-digit
- 2 status LEDs
- 3 programming button
- 4 Aseptoflex sealing edge
- 5 Aseptoflex thread



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2			
Measuring range	-1...10 bar	-14.5...145 psi	-100...1000 kPa	-0.1...1 MPa
Process connection	threaded connection Aseptoflex external thread Aseptoflex			

Application

Special feature	Gold-plated contacts
Application	flush mountable for the food and beverage industry
Installation	freely rotatable housing 350°
Media	viscous media and liquids with suspended particles; liquids and gases



Flush pressure sensor with display

PI-010-RES30-QFRKG/US/ /P

Medium temperature	[°C]	-25...125; (145 max. 1h)		
Min. bursting pressure		150 bar	2175 psi	15 MPa
Pressure rating		50 bar	725 psi	5 MPa
Type of pressure		relative pressure		
No dead space		yes		

Electrical data				
Operating voltage	[V]	18...32 DC		
Current consumption	[mA]	< 50		
Min. insulation resistance	[MΩ]	100; (500 V DC)		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	0.5		
Integrated watchdog		yes		

Inputs / outputs	
Number of inputs and outputs	Number of digital outputs: 2

Outputs	
Total number of outputs	2
Output signal	switching signal
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V] 2
Permanent current rating of switching output DC	[mA] 250
Switching frequency DC	[Hz] 85
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Measuring/setting range				
Measuring range	-1...10 bar	-14.5...145 psi	-100...1000 kPa	-0.1...1 MPa
Set point SP	-0.98...10 bar	-14.2...145 psi	-0.098...1 MPa	
Reset point rP	-1...9.98 bar	-14.5...144.7 psi	-0.1...0.998 MPa	
In steps of	0.01 bar	0.1 psi	0.001 MPa	
Factory setting		SP1 = 2.50 bar	rP1 = 2.30 bar	
		SP2 = 7.50 bar	rP2 = 7.30 bar	

Accuracy / deviations	
Switch point accuracy	< ± 0,2; (Turn down 1:1)
[% of the span]	
Repeatability	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)
[% of the span]	
Characteristics deviation	< ± 0,2; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)
[% of the span]	
Linearity deviation	< ± 0,15; (Turn down 1:1)
[% of the span]	
Hysteresis deviation	< ± 0,15; (Turn down 1:1)



Flush pressure sensor with display

PI-010-RES30-QFRKG/US/ /P

[% of the span]		
Long-term stability		< ± 0,1; (Turn down 1:1; per year)
	[% of the span]	
Temperature coefficient zero point		< ± 0,05; (0...70 °C)
	[% of the span / 10 K]	
Temperature coefficient span		< ± 0,15; (0...70 °C)
	[% of the span / 10 K]	
Response times		
Response time	[ms]	< 6
Damping process value dAP	[s]	0...100
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; zero point; span	
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67; IP 69K
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5/1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[years]	178
Mechanical data		
Weight	[g]	405.5
Housing		cylindrical
Dimensions	[mm]	Ø 34 / L = 119
Materials		stainless steel (316L/1.4404); PC; PBT; PEI; FKM; PTFE
Materials (wetted parts)		ceramics (99.9 % Al2O3); stainless steel (316L/1.4435); surface characteristics: Ra < 0,4 / Rz 4; PTFE
Min. pressure cycles		100 million
Process connection		threaded connection Aseptoflex external thread Aseptoflex
Displays / operating elements		
Display	Display unit	4 x LED, green
	switching status	2 x LED, yellow
	measured values	alphanumeric display, 4-digit
	parameter setting	alphanumeric display, 4-digit
Display unit		bar; psi; MPa; % of the span
Remarks		
Remarks	The 3-A qualification is only valid if adapters with 3-A qualification are used for installation.	
Notes	Please do not use for new projects.; no more adapters available as accessories	
Pack quantity	1 pcs.	

PI7094





Flush pressure sensor with display

PI-010-RES30-QFRKG/US/ /P

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



OUT1	switching output Diagnostic output
OUT2	switching output