


MVQ101



Position sensor for valve actuators

SVS BASIC IO-LINK



Product characteristics	
Communication interface	IO-Link
Housing	rectangular
Dimensions [mm]	95 x 50 x 57
Switching outputs	
Electrical design	PNP
Output function	3 x normally open / normally closed; (selectable)
Application	
Operating principle	magnetic
Application	angle of rotation detection absolute
Electrical data	
Operating voltage [V]	10...30 DC



Position sensor for valve actuators

SVS BASIC IO-LINK

Current consumption	[mA]	< 40
Protection class		III
Reverse polarity protection		yes
Max. power-on delay time	[ms]	300
Outputs		
Switching outputs		
Electrical design		PNP
Output function		3 x normally open / normally closed; (selectable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Short-circuit protection		yes
Overload protection		yes
Detection zone		
Detection zone	[°]	360
Accuracy / deviations		
Rotational angle detection		
Accuracy	[°]	± 1
Resolution	[°]	0.1
Temperature drift	[°/K]	0,02
Repeatability	[°]	0,1
Switch point indication		
Tolerance	[°]	0.1...15; (Factory setting: 10)
Hysteresis	[°]	0.1...5; (Factory setting: 3)
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9 CDV
Profiles		Smart Sensor: Device Identification; Device Diagnosis; Device Teach Channel; Binary Data Channel; Process Data Variable; Blob; Measurement Data Channel
SIO mode		yes
Required master port type		A
Min. process cycle time	[ms]	4
Supported DeviceIDs	Type of operation	DeviceID
	default	595
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 65; IP 67; (Target puck area dust-protected)

MVQ101



Position sensor for valve actuators

SVS BASIC IO-LINK

Tests / approvals		
EMC	EN 61000-4-2	4 kV CD / 8 kV AD
	EN 61000-4-3	10 V/m
	EN 61000-4-4	2 kV
	EN 61000-4-6	10 V
	EN 55011	class B
Vibration resistance	EN 60068-2-6 Fc	1 mm (10...55 Hz) / 1 octave per minute in 3 axes
Shock resistance	EN 60068-2-27 Ea	30 g 11 ms half sine; 6 shocks each in every direction along the three coordinate axes
MTTF [years]		410
Embedded software included		yes
UL approval	UL Approval no.	S001
Mechanical data		
Weight [g]		175
Housing		rectangular
Dimensions [mm]		95 x 50 x 57
Materials		housing, target puck: PA; plug: stainless steel (316L / 1.4404)
Tightening torque [Nm]		target puck: 1,2; housing: 3,0; housing on plastic mounting plate: 0,9
Displays / operating elements		
Display	operation	1 x LED, green
	switching status	3 x LED, white
	switching status	1 x LED, RGB
Accessories		
Items supplied		socket head screws: 4 x M5 x 16, stainless steel
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		
Connector: 1 x M12; coding: A; Moulded body: stainless steel		


MVQ101



Position sensor for valve actuators

SVS BASIC IO-LINK

Connection



1	L+
2	Out2
3	L-
4	Out1 IO-Link
5	Out3