


O5D152



Photoelectric distance sensor

O5DLCNKG/US



Product characteristics		
Type of light		red light
Laser protection class		1
Housing		rectangular
Application		
Special feature		Background suppression
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	75; (24 V)
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	650
Typ. lifetime	[h]	50000



Photoelectric distance sensor

O5DLCNKG/US

Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 2	
Outputs			
Total number of outputs		2	
Electrical design		NPN	
Number of digital outputs		2	
Output function		normally open / normally closed; (complementary)	
Max. current load per output	[mA]	100	
Switching frequency DC	[Hz]	11	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Detection zone			
Max. light spot diameter	[mm]	5	
Light spot dimensions refer to		2 m	
Detection range hysteresis	[%]	< 4	
Note on monitoring range hysteresis		black 6% remission	
Background suppression available		yes	
Background suppression	[m]	< 20	
Measuring/setting range			
Measuring range	[m]	0.03...2	
Sampling rate	[Hz]	33	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9	
SIO mode		yes	
Process data binary		2	
Min. process cycle time	[ms]	6.6	
Supported DeviceIDs		Type of operation	DeviceID
		default	372
Operating conditions			
Ambient temperature	[°C]	-25...60	
Note on ambient temperature		at ta < -10 °C warm-up is necessary, laser is off	
Protection		IP 65; IP 67	
Max. immunity to extraneous light	[klx]	10; (on the object)	
Tests / approvals			
EMC		EN 60947-5-2	
Vibration resistance		DIN EN 60068-2-6	10 g (10...55 Hz) / 120 min. per axis (x, y, z)
Shock resistance		DIN EN 60068-2-27	50 g 6 shocks / 11 ms half-sine (x, y, z)

O5D152



Photoelectric distance sensor

O5DLCNKG/US

Laser protection class	1	
Notes on laser protection	Caution:	laser light
	laser class:	1
		EN / IEC60825-1:2007
		EN / IEC60825-1:2014
		Complies with 21 CFR 1040 except for deviations pursuant to Laser Notice No. 50, dated June 2007.
MTTF [years]	151	

Mechanical data

Weight [g]	76.5	
Housing	rectangular	
Dimensions [mm]	56 x 18.2 x 46.8	
Materials	housing: PA; bezel: stainless steel; operator interface: TPU; lens: PMMA	
Lens alignment	side lens	

Displays / operating elements

Display	switching status	LED, yellow switching output PIN 4
	operation	LED, green
	display	alphanumeric display, 3-digit
Display unit	cm	

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



Connection



4: OUT / IO-Link



Photoelectric distance sensor

O5DLCNKG/US

Other data

accuracy

	accuracy			
distance	black (6 % remission)	white (90 % remission)		
0 mm	± 25 mm	± 25 mm		
500 mm	± 25 mm	± 25 mm		
1000 mm	± 25 mm	± 25 mm		
1500 mm	± 40 mm	± 30 mm		
2000 mm	± 50 mm	± 30 mm		
Extraneous light on the object		< 10 klx		

Diagrams and graphs

hysteresis graph

