


OGS700



Through-beam laser sensor transmitter

OGSLOOKG/US100



Product characteristics

Type of light	red light
Laser protection class	1
Housing	threaded type

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	13
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	655
Typ. lifetime	[h]	50000

Detection zone

Transmitter / receiver		transmitter
Range	[m]	< 60
Range adjustable		no
Diameter of the smallest detectable object	[mm]	3; (60 m)
Max. light spot diameter	[mm]	312
Light spot dimensions refer to		at maximum range

Operating conditions

Ambient temperature	[°C]	-10...60
Protection		IP 65; IP 67

Tests / approvals

EMC	EN 60947-5-2	
Laser protection class		1



Through-beam laser sensor transmitter

OGSLOOKG/US100

Notes on laser protection	Caution:	laser light
	laser class:	1
		EN / IEC60825-1:2007
		EN / IEC60825-1:2014
		Complies with 21 CFR 1040 except for deviations pursuant to Laser Notice No. 50, dated June 2007.
MTTF	[years]	1018

Mechanical data

Weight	[g]	64.3
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 72
Thread designation		M18 x 1
Materials		stainless steel (316L/1.4404); PA; EPDM
Lens material		PMMA

Displays / operating elements

Display	operation	1 x LED, green
---------	-----------	----------------

Accessories

Items supplied		lock nuts: 2
----------------	--	--------------

Remarks

Remarks		operating voltage "supply class 2" according to cULus
Pack quantity		1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection

