


Diffuse reflection sensor

OGT-DNKG/US



- 1 potentiometer receiver in upper lens transmitter in lower lens



Product characteristics

Type of light	red light
Housing	threaded type

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	20
Protection class	III
Reverse polarity protection	yes
Type of light	red light

Outputs

Electrical design	NPN
Output function	dark-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Overload protection	yes

Detection zone

Range [mm]	10...400; (white paper 200 x 200 mm 90% remission)
Setting range [mm]	70...400
Range adjustable	yes
Max. light spot diameter [mm]	25
Light spot dimensions refer to	at maximum range

OGT103



Diffuse reflection sensor

OGT-DNKG/US

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 65; (in conjunction with a corresponding connector)

Tests / approvals

EMC		EN 60947-5-2
MTTF	[years]	894

Mechanical data

Weight	[g]	14.6
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 44
Thread designation		M18 x 1
Materials		housing: ABS
Lens material		PMMA

Displays / operating elements

Display	switching status	1 x LED, yellow
Operating elements		potentiometer

Accessories


Items supplied		lock nuts: 2
----------------	--	--------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Connector: 1 x M12; coding: A



Connection

