



Pressure switch with intuitive switch point setting

PK-100-SFP14-HCPKG/US/ /W



1 Tightening torque 25 Nm



Product characteristics		
Number of inputs and outputs	Number of digital outputs: 2	
Measuring range	0...100 bar	0...10 MPa
Process connection	threaded connection R 1/4 external thread internal thread:M5	
Application		
Application	for industrial applications	
Media	liquids and gases	
Medium temperature [°C]	-25...80	
Min. bursting pressure	1000 bar	100 MPa
Pressure rating	200 bar	20 MPa
Type of pressure	relative pressure	
Electrical data		
Operating voltage [V]	9.6...32 DC	
Current consumption [mA]	< 25	
Min. insulation resistance [MΩ]	100; (500 V DC)	
Protection class	III	
Reverse polarity protection	yes	
Inputs / outputs		
Number of inputs and outputs	Number of digital outputs: 2	
Outputs		
Total number of outputs	2	
Output signal	switching signal	
Electrical design	PNP	
Number of digital outputs	2	
Output function	complementary	



Pressure switch with intuitive switch point setting

PK-100-SFP14-HCPKG/US/ /W

Max. voltage drop switching output DC	[V]	2	
Permanent current rating of switching output DC	[mA]	500	
Switching frequency DC	[Hz]	100	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Measuring range		0...100 bar	0...10 MPa
Set point SP		5...100 bar	0.5...10 MPa
Reset point rP		3...98 bar	0.3...9.8 MPa
Accuracy / deviations			
Switch point accuracy		< ± 2,5; (Setting accuracy)	
[% of the final value]			
Repeatability		< ± 0,5; (with temperature fluctuations < 10 K)	
[% of the final value]			
Characteristics deviation		< ± 1,5 (BFSL) / < ± 2,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)	
[% of the final value]			
Temperature drift per 10 K		< ± 0.5	
Software / programming			
Adjustment of the switch point		setting rings	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Storage temperature	[°C]	-40...100	
Protection		IP 67	
Tests / approvals			
EMC		DIN EN 61000-6-2	
		DIN EN 61000-6-3	
Shock resistance		DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance		DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[years]	713	
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data			
Weight	[g]	93.5	
Housing		cylindrical	
Dimensions	[mm]	Ø 27 / L = 70.6	
Materials		PBT; PC; FKM; stainless steel (316L/1.4404)	
Materials (wetted parts)		stainless steel (316L/1.4404)	
Min. pressure cycles		50 million	
Process connection		threaded connection R 1/4 external thread internal thread:M5	
Restrictor element integrated		no (can be retrofitted)	

PK6732



Pressure switch with intuitive switch point setting

PK-100-SFP14-HCPKG/US/ /W

Displays / operating elements


Display	operation	LED, green
	switching status	LED, yellow
With scale		yes

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



Connection

