


PQ3809



Pressure sensor for pneumatics

PQ-1-1-KHR18-KFPKG/AS/



- 1 main pressure connection G 1/8 Tightening torque < 8 Nm insertion depth < 7.5 mm
- 2 auxiliary pressure connection M 5 Tightening torque < 2.5 Nm insertion depth < 7.5 mm
- 3 Tightening torque < 0.5 Nm
- 4 LEDs Display unit / switching status
- 5 alphanumeric display 4-digit
- 6 programming button



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1				
Measuring range	-1...1 bar	-1000...1000 mbar	-14.6...14.6 psi	-29.4...29.4 inHg	-100...100 kPa
Process connection	threaded connection G 1/8 internal thread internal thread:M5				

Application

Special feature	Gold-plated contacts			
Application	for industrial applications			
Conditionally suitable for	other media on request			
Medium temperature [°C]	0...60			
Min. bursting pressure	30 bar	435 psi	886 inHg	3000 kPa
Note on min. burst pressure	max. overpressure on second pressure connection: 12 bar / 1200 kPa / 174 PSI / 354,4 inHg / 1,2 MPa			
Pressure rating	20 bar	290 psi	591 inHg	2000 kPa
Vacuum resistance [mbar]	-1000			



Pressure sensor for pneumatics

PQ-1-1-KHR18-KFPKG/AS/

Vacuum resistance	[MPa]	-0.1				
Type of pressure		relative pressure; differential pressure; vacuum				
Electrical data						
Operating voltage	[V]	18...32 DC; (to SELV/PELV)				
Current consumption	[mA]	< 50				
Min. insulation resistance	[MΩ]	100; (500 V DC)				
Protection class		III				
Reverse polarity protection		yes				
Overvoltage protection		yes; (< 40 V)				
Power-on delay time	[s]	0.5				
Integrated watchdog		yes				
Inputs / outputs						
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1				
Outputs						
Total number of outputs		2				
Output signal		switching signal; analogue signal; IO-Link; (configurable)				
Electrical design		PNP				
Number of digital outputs		1				
Output function		normally open / normally closed; (parameterisable)				
Max. voltage drop switching output DC	[V]	2				
Permanent current rating of switching output DC	[mA]	100				
Switching frequency DC	[Hz]	< 100				
Number of analogue outputs		1				
Analogue current output	[mA]	4...20				
Max. load	[Ω]	500				
Short-circuit protection		yes				
Type of short-circuit protection		pulsed				
Measuring/setting range						
Measuring range		-1...1 bar	-1000...1000 mbar	-14.6...14.6 psi	-29.4...29.4 inHg	-100...100 kPa
Set point SP		-0.98...1 bar	-14.2...14.6 psi	-28.8...29.4 inHg	-98...100 kPa	
Reset point rP		-0.99...0.99 bar	-14.4...14.4 psi	-29.1...29.1 inHg	-99...99 kPa	
In steps of		0.01 bar	0.2 psi	0.3 inHg	1 kPa	
Accuracy / deviations						
Switch point accuracy		< ± 0,5				
	[% of the span]					
Repeatability		< ± 0,1; (with temperature fluctuations < 10 K)				
	[% of the span]					
Characteristics deviation		< ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)				
	[% of the span]					
Hysteresis deviation		< ± 0,25				
	[% of the span]					
Long-term stability		< ± 0,05; (per 6 months)				
	[% of the span]					



Pressure sensor for pneumatics

PQ-1-1-KHR18-KFPKG/AS/

Temperature coefficient zero point [% of the span / 10 K]	0,2; (0...60 °C)				
Temperature coefficient span [% of the span / 10 K]	0,2; (0...60 °C)				
Response times					
Response time [ms]	< 6				
Delay time programmable dS, dr [s]	0; 0,002...5				
Step response time analogue output [ms]	6				
Software / programming					
Parameter setting options	hysteresis / window; normally open / normally closed; analogue output; IO-Link; switching logic; switch-on/switch-off delay; Damping; Display unit				
Interfaces					
Communication interface	IO-Link				
Transmission type	COM2 (38,4 kBaud)				
IO-Link revision	1.1				
SDCI standard	IEC 61131-9 FDIS				
Profiles	Smart Sensor: Process Data Variable; Device Identification				
SIO mode	yes				
Required master port type	A				
Process data analogue	1				
Process data binary	2				
Min. process cycle time [ms]	2.3				
Supported DeviceIDs	<table> <tr> <th>Type of operation</th><th>DeviceID</th></tr> <tr> <td>default</td><td>366</td></tr> </table>	Type of operation	DeviceID	default	366
Type of operation	DeviceID				
default	366				
Operating conditions					
Ambient temperature [°C]	0...70				
Storage temperature [°C]	-25...85				
Protection	IP 65				
Tests / approvals					
EMC	<table> <tr> <td>DIN EN 61000-6-2</td><td></td></tr> <tr> <td>DIN EN 61000-6-3</td><td></td></tr> </table>	DIN EN 61000-6-2		DIN EN 61000-6-3	
DIN EN 61000-6-2					
DIN EN 61000-6-3					
Shock resistance	DIN EN 60068-2-27 50 g (11 ms)				
Vibration resistance	DIN EN 60068-2-6 20 g (10...2000 Hz)				
MTTF [years]	437				
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request				
Mechanical data					
Weight [g]	87				
Housing	rectangular				
Dimensions [mm]	42 x 30 x 32				
Materials	PBT; FKM; polyester				
Materials (wetted parts)	brass; FKM; silicon (coated); PBT				
Min. pressure cycles	50 million				

PQ3809



Pressure sensor for pneumatics

PQ-1-1-KHR18-KFPKG/AS/

Process connection	threaded connection G 1/8 internal thread internal thread:M5
--------------------	--

Displays / operating elements


Display	Display unit	4 x LED, green
	switching status	1 x LED, yellow
	function display	alphanumeric display, 4-digit
	measured values	alphanumeric display, 4-digit
Display unit	bar; kPa; psi; inHg	

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M8; coding: A; Contacts: gold-plated



Connection



OUT1	switching output IO-Link
OUT2	analogue output