











Digital Outputs 0-5 are parallel to Relay Outputs 0-5



Signal Inputs
Logic "0" level: 0V - 3,6V (Vin=12V), 0V-7,2V (Vin=24V)
Logic "1" level: 9V - 13,2V (Vin=12V), 18V-26,4V (Vin=24V)
Maximum input current <3mA
Voltage range in case of analog input use
0 - 13,2V (Vin=12V) / 0 - 26,4V (Vin=24V)



A4 + A5 only Analog Inputs



Pin Header current limit:

Absolute max per pin 40mA
recommended 20mA

Absolute max 200mA
for entire Pin Header

Current limit @5V + 3V3 max
200mA (Fused by resettable fuse)
Current limit @3V3 only 150mA

All signals are protected with serial resistance



MINI

PINOUT V1.1

