








SECTION A-A



Dimension

Dim L	N×5.0
Dim B	(N-1)×5.0
Dim C	(N+2)×5.0
Dim D	(N+1)×5.0

N= Number of poles

Poles	Tolerance Dim L/B/C/D
2P-5P	±0.15
6P-10P	±0.20
11P-15P	±0.25
16P-20P	±0.30
21P-24P	±0.40

REV	DATE	ECN NO.	APPROVER
E	04/12-21	ECN202104004	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item a Terminal body:Thermoplastic (UL94V-0)
- Item b Terminal cover:Thermoplastic (UL94V-0)
- Item c Female contact:PhBz,Bright Tin plated over Nickel plated
- Item d Terminal body:Brass, Ni plated
- Item e Terminal screw:Steel Zinc plating "-" slot type
- Item f With flange screw:Steel Zinc plating M2.5"/+/-" slot type

Electrical

- Voltage rating:300V
- Current rating:12A
- Solid wire(AWG):12-24
- Stranded wire(AWG):12-24
- Torque(Lb-In): 5
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: us
- Critical dimension: ▲

TJ xx 7 1 x 7 xxxx G

No. OF POLES
02: 2 POLES
:
:
24: 24 POLES

COLOR
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)


G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

**Amphenol
ANYTEK**

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TJ 5.0 Series With flange contact on up side					
PART NO.	TJxx71x7xxxxG			DWG NO.	8TJ0902		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Chen Bo 04/12-21	Chen Bo 04/12-21			UNIT: mm	X. ±0.50
				SHEET: 01/01		SCALE: NONE	X.X ±0.30
						REV.: E	X.XX ±0.10
							X° ±1°