


RoHS Compliant



No. OF POLES
02: 2 POLES
... ..
24: 24 POLES



TS xx 51x C xxxx G

8 Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo
000A: "ANYTEK" Mark
0091: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.




SECTION P-P

N = Number of poles

Dim A	NX5.08±0.5	
Dim B	(N-1)X5.08	
Dim C	NX5.08	

Poles	Dim A/B/C TOL	
2-6p	±0.15	±0.15
7-12p	±0.20	±0.20
13-18p	±0.30	±0.30
19-24p	±0.40	±0.40



REV	SIGN	DATE	DESCRIPTION	APPROVER
D	8	11/01'05	Standard spec is changed.	Marivn
E	8	8/07'06	Added VDE and TUV standard	梁仁松
F	8	12/02'08	With flange screw changed from "-" slot type to "+/-" slot type	Jacke
	8	12/02'08	The temperature changed from -30°C, +105°C to -40°C, +115°C	Jacke
	8	12/02'08	Add the tolerance table	Jacke
G	8	2010.03.12	Add the 2p mark	Jacke
H	8	2010.08.16	The design is changed	Chen Bo
I	8	08/06-20	update the drawing	Chen Bo


THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item 8 Clamp: Brass(CuZn), Ni plating
- Item 6 Terminal screw: Steel Cr3+ Zinc plating "-" slot type
- Item 7 Female contact: PhBz, Bright Tin plated over Nickel plated
- Item 4 Terminal up body: Thermoplastic (UL94V-0)
- Item 5 Terminal down body: Thermoplastic (UL94V-0)
- Item 6 With flange screw : Steel Zinc plating M2.5 "+/-" slot type

1 2 Electrical cULus/VDE/TUV

- Voltage rating: 300VAC/300VAC/300VAC
- Current rating: 15A/17A/15A
- Wire range: 2.5mm /0.34-2.5mm²
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 3.5Lb-In./0.5Nm/0.4Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval: cULus VDE TUV
- Critical dimension: 8

**Amphenol**
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TS-5.08mm Series(W/latching hooks on the wire entry side) with flange						
PART NO.		TSxx51xCxxxxG		DWG NO.	8TS0103			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Chen Bo 08/06-20	Chen Bo 2010.08.16		UNIT: mm		X.	±0.50
					SCALE: NONE		X.X	±0.30
							X.XX	±0.10
SHEET: 01/01		REV: I				X°	±1°	