





RoHS Compliant



P.C.B LAYOUT



N=Number of contacts

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
C	△	07/27'20	Update the drawing frame	Rhine
	△	07/27'20	Add TUV certification	Rhine
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Material:

- Item 1 Terminal housing: Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass ,Ni plated
- Item 3 Wire guard solder pin: Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

△ Electrical cULus TUV

- Voltage rating: 300VAC 250VAC
- Current rating: 16A 17.5A
- Wire range: 0.2-1.5mm²
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Torque: 3.5Lb-In. 0.5N.m
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV 2.0KV
- Operating temperature: -40°C to +115°C
- Wave soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus △
- Critical dimension: ▲

VI xx 21 x 3 xxxx G

			Pb < 40,000ppm (RoHS)
04 4 CONTACTS	0 Black (RAL9005)	0000:"@Logo (Standard)	
05 5 CONTACTS	2 Red (RAL3001/D)	000A:"ANYTEK"Logo	
... ..	3 Orange(RAL2011/P)	Any special item by	
24 24 CONTACTS	4 Yellow(RAL1018/A)	customer request,	
	5 Green(RAL6018/T)	please contact sales	
	6 Blue (RAL5015/A)	department.	
	8 Grey(RAL7035/D)		

Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim A			20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96	66.04
Dim B			15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96
TOL	±0.10				±0.15				±0.20			
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim A	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	121.92	
Dim B	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	
TOL	±0.20		±0.25				±0.30					

**Amphenol
ANYTEK****CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VI 5.08 SERIES 4P-24P 90° wire inlet Vertical-solid block(without cover)						
PART NO.		VIxx21x3xxxxG			DWG NO.		8VI0303	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
			Rhine 2020.07.27	Rhine 2020.07.27		UNIT: mm		X. ±0.50
						SCALE: NONE		X.X ±0.30
						SHEET: 01/01		X.XX ±0.10
						REV.: C		X° ±1°