


DIGITUS CAT 8.2 S/FTP installation cable, 500 m, Simplex, Dca-s2,d1,a1

DK-1843-VH-5
EAN 4016032380542



CAT 8.2 S-FTP installation cable, 2000 MHz, AWG 22/1 Dca, 500 m, drum, simplex, grün

The Digitus Cat 8.2 S/FTP installation cable is designed for use in the structured data center and the building cabling according to ISO/IEC 11801, DIN EN 50288-12-1, DIN EN 50173, IEC 60332-3-24. The cable is perfectly suitable for the transmission of both analog and digital data and also supports POE. The shielding structure is composed of single shielded pairs with a tinned copper braid, which ensures excellent shielding and electrical values.

Future-oriented standards and high-end quality for your network

- Physical properties:
- Conductor: Bare copper wire, AWG 22/1
- System(s) of assessment and verification of constancy of performance: System 3
- Insulation: SFS-PE (foamed polyethylene jacket)
- Total number of insulated conductors: 8, twisted into 4 pairs
- Color code: Blue-white, orange-white, green-white, brown-white
- Shielding of the individual pairs: Aluminum-laminated polyester film, covers 100%
- Overall shielding: Tinned copper braiding
- Outer sheath: Dca-s2,d1,a1 according to EN 50575
- Outer sheath thickness (nominal): 0.55 mm nominal
- Outer sheath color: Green
- Mechanical properties:
- Strain relief: 150N max.
- Dynamic bending radius: 8x AD mm min.
- Static bending radius: 4x AD mm min.
- Transport and storage temperature range: -20 °C to +75 °C

- Operating temperature range: -20 °C to +60 °C
- Installation temperature range: 0 °C to +50 °C
- Outer diameter simplex (nominal): 7.9 mm nominal (Dca)
- Weight (kg/km): 65 kg/km
- Electrical properties:
- Impedance: 100±15 Ohm @ 1 - 2000 MHz
- Capacitance: 99 pF/30m nominal @ 1 KHz
- Capacitance unbalance (pair-earth): 99pF/30m max. @ 1 KHz
- Insulation resistance: 5 GOhm x km min.
- DC resistance: 2.4 Ohm/30m max. (4% max. unbalanced resistance)
- Loop resistance: 5.6 Ohm/24m max. (3% max. unbalanced resistance)
- Operating voltage: 72 Vdc max.
- Coupling attenuation: CA-Type 1
- Phase delay: 171 nS/30 m max.
- Time delay: 13.5 nS/130 m max.
- Separation class: "d" according to EN 50174-2
- NVP: 79%
- Assortment: Twisted Pair Installation Cables
- Category: CAT 8.2
- Shielding: S-FTP, pairs in metal foil and braid shielding
- CPR: Dca
- Length: 500 m
- Color: green
- Jacket: LSOH
- Structure: 4 x 2 AWG 22/1, solid twisted pair

Package contents





- CAT 8.2 S/FTP installation cable on drum, 500 m, Simplex, Dca

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	1	30.00	34.00	39.50	39.50	53,048.50
Packaging Unit Inside	1	30.00	34.00	39.50	39.50	53,048.50
Packaging Unit Single	1	30.00	34.00	39.50	39.50	53,048.50
Net single without Packaging	1	0.00	0.00	0.00	0.00	0.00

The diagram illustrates the frequency ranges for various Ethernet standards, categorized by their maximum supported frequency. The standards are represented by colored horizontal bars, with their respective frequency ranges indicated by the labels above them:

- CAT 6.0:** 1 to 250 MHz (Blue bar)
- CAT 6:** 1 to 250 MHz (Orange bar)
- CAT 5E:** 1 to 100 MHz (Green bar)
- CAT 5:** 1 to 100 MHz (Yellow bar)
- CAT 4:** 1 to 100 MHz (Red bar)
- CAT 3:** 1 to 100 MHz (Purple bar)
- CAT 2:** 1 to 100 MHz (Pink bar)
- CAT 1:** 1 to 100 MHz (Light blue bar)

The diagram also shows the frequency ranges for CAT 6.0, CAT 6, CAT 5E, CAT 5, CAT 4, CAT 3, CAT 2, and CAT 1. The frequency ranges are: CAT 6.0: 1 to 250 MHz; CAT 6: 1 to 250 MHz; CAT 5E: 1 to 100 MHz; CAT 5: 1 to 100 MHz; CAT 4: 1 to 100 MHz; CAT 3: 1 to 100 MHz; CAT 2: 1 to 100 MHz; CAT 1: 1 to 100 MHz.

[illegible]

DIGITUS

