

NJ	XX	X	X	X	0	X	X	X	X	X
	Number of contacts	Pitch	PCB mounting	Color						
End Stackable 01 1 contacts 02 2 contacts 03 3 contacts 24 24 contacts	0 5.0/.197" 2 3.5/.138"	0 Vertical (90D wire inlet) 1 Horizontal (180D wire inlet)	0 Black 2 Red (RAL 3001/D) 5 Green (RAL 6018/T) 8 Grey (RAL 7004/P) C Multiple colors	0000 Standard Any special item by customer request, please contact sales department.		G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy				

NK	XX	X	X	X	X	X	X	X	X	X
	Number of contacts	Pitch	PCB mounting	Color	Tail type					
End Stackable 01 1 contacts 02 2 contacts 03 3 contacts 16 16 contacts	A 7.5/.295"	0 Vertical (90D wire inlet) 1 Horizontal (180D wire inlet)	0 Black 5 Green (RAL 6018/T) 6 Blue (RAL 5015/A) 8 Grey (RAL 7004/P)	0 Parallel tail(A type) 1 Interlace tail(B type) (Front contact link together with end cover) 2 Interlace tail(C type) (After contact link together with end cover)		0000 Standard Any special item by customer request, please contact sales department.		G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy		

NL	XX	X	X	X	X	X	X	X	X	X
	Number of contacts	Pitch	Current	Color	Body type					
Solid Block 04 2*2 contacts 48 2*24 contacts (current 5A) 28 2*14 contacts (current 8A, With flange) 32 2*16 contacts (current 8A, W/O flange) 28 2*14 contacts (With operating lever)	1 3.5/.138"	0 Low current(5A) (only With flange & W/O flange type) 1 High current(8A)	0 Black 2 Red 3 Orange 4 Yellow 5 Green (RAL 6018/T) 6 Blue 8 Grey 9 White C Green (RAL 6018/U)	1 With flange 2 W/O flange 3 With operating lever		0000 Standard Any special item by customer request, please contact sales department.		G RoHS compliant (lead<4%) In copper Alloy H RoHS compliant (lead<1000ppm) In copper Alloy		

NM	XX	X	0	X	X	X	X	X	X	X
	Number of contacts	Pitch		Color	Wire inlet					
End Stackable 02 2 contacts 03 3 contacts 24 24 contacts	1 3.5/.138"	THR type 0 Black DIP type 0 Black 6 Blue 2 Red 8 Grey 3 Orange 9 White 4 Yellow C Green 5 Green (RAL 6018/U) (RAL 6018/T)	THR type A Vertical(90D wire inlet) B Horizontal(180D wire inlet) C Slope(45D wire inlet) DIP type 0 Vertical(90D wire inlet) 1 Horizontal(180D wire inlet) 2 Slope(45D wire inlet)		0000 Standard Any special item by customer request, please contact sales department.		G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy			

NP	XX	X	X	X	X	X	X	X	X	X
	Number of contacts	Pitch	PCB mounting	Color	Tail type					
End Stackable 01 1 contacts 02 2 contacts 03 3 contacts 16 16 contacts	1 10.0/.393"	0 Vertical (90D wire inlet) 1 Horizontal (180D wire inlet)	0 Black 5 Green (RAL 6018/T) 6 Blue (RAL 5015/A) 8 Grey (RAL 7004/P)	0 Parallel tail(A type) 1 Interlace tail(B type) (Front contact link together with end cover) 2 Interlace tail(C type) (After contact link together with end cover)		0000 Standard Any special item by customer request, please contact sales department.		G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy		