





(b)

plating pos. 2	part no.
GOLD FLASH over NICKEL	131A13039X
min. 20µin HARD GOLD over min. 50µin NICKEL	131B13039X
min. 30µin HARD GOLD over min. 50µin NICKEL	131C13039X

3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
2	1	MATING SIDE	COPPER ALLOY	SEE TABLE
1	1	REAR SIDE	COPPER ALLOY	TIN PLATED
pos	qty	description	material	plating

partlist									
tolerance ISO 2768-m									
 dim. in mm									
scale: 8:1									
material: SEE PARTLIST									
title: HIGH POWER CONTACT MALE SOLDER PIN 90°, d=3.75, 40A D-SUB COMBINATION									
dwg no:									
13K1IE2A									
part no: SEE TABLE									
DO NOT ALTER CAD DRAWING BY HAND									
1 x b A4680 06.03.2013 K.H.									
a Original									
rev. description date name									
CONEC®									

Directive 2002/95/EC RoHS compliant