



1	1	MATING SIDE	COPPER ALLOY	min. 30µin HARD GOLD over min. 50µin NICKEL
2	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
3	1	PLUG CONTACT SOLDER PIN 90°	COPPER ALLOY	TIN PLATED
pos	qty	description	material	plating
partlist				
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			tolerance	scale: 5 : 1
			dim. in mm	material: see partlist
			date	name
			drawn 09.09.10	Henneboel
			appd. 09.09.10	Koch
DO NOT ALTER CAD DRAWING BY HAND			norm	title: HIGH POWER CONTACT MALE PREMATING SOLDER PIN 90°, d=1,9mm, 15A D-SUB COMBINATION
			d-old	dwg no: Inventor 10
			a	Origin
			rev.	description
			date	name
			CONEC	
			part no: 131C13109X	

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	