



STRIPPING DIMENSION



Directive 2002/95/EC
RoHS
Compliant

3	1	MATING SIDE	COPPER ALLOY	min. 30µin HARD GOLD over min. 50µin NICKEL
2	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
1	1	REAR SIDE	COPPER ALLOY	GOLD FLASH over NICKEL
POS	QTY	DESCRIPTION	MATERIAL	PLATING

PARTLIST

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND					tolerance		 dim. in mm	scale: 5:1		
								material: SEE TABLE		
						date	name	title: HIGH POWER CONTACT MALE CRIMP / SOLDER VERSION 90° - 20A D-SUB COMBINATION PREMATING		
					drawn	30.09.10	Henneboel			
					appd.	30.09.10	Koch			
					norm					
					d-old					
							dwg no:		Inventor	DIN-A3 sh: 1
							part no:		131C16129X	
		rev.	description	date	name					

CONEC