







STRIPPING DIMENSIONS



Directive 2002/95/EC
„RoHS“
Compliant

NOTES:

1. MATERIAL: COPPER ALLOY
2. PLATING:
ITEM 1: NICKEL PLATED
ITEM 2+3: 8µin HARD GOLD over min. 50µin NICKEL

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		dim. in mm		scale: 5:1	
DO NOT ALTER CAD DRAWING BY HAND				date		name		material: SEE NOTES	
rev.				description		date		title:	
1				13K1A3027		10.12.09		HIGH POWER CONTACT FEMALE	
2				13K1A3027		10.12.09		CRIMP / SOLDER VERSION 90° - 10A	
3				13K1A3027		10.12.09		D-SUB COMBINATION	
4				13K1A3027		10.12.09		dwg no: Inventor	
5				13K1A3027		10.12.09		DIN-A3	
6				13K1A3027		10.12.09		sh: 1	
7				13K1A3027		10.12.09		part no: 132A16019X	
8				13K1A3027		10.12.09		part no: 132A16019X	

CONEC