




NOTES:

1. MATERIAL:

ITEM 1+2: COPPER ALLOY

ITEM 3: STAINLESS STEEL

2. PLATING:

ITEM 1: SEE TABLE

ITEM 2: TIN PLATED

PLATING ITEM 1	PART-NO.
8µ" HARD GOLD OVER min. 50µ" NICKEL	132A13070X
30µ" HARD GOLD OVER min. 50µ" NICKEL	132C13070X

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Original		

tolerance	dim. in mm
date	name
drawn 22.06.2004	Schmidt
appd. 22.06.2004	Mickenbecker
norm	
d-old	

CONEC®

scale:	5:1
material:	SEE NOTES
title:	HIGH POWER CONTACT FEMALE SOLDER PIN 90°, Ø 3,2 , 30A D-SUB COMBINATION
dwg no:	13K1A1156
part no:	SEE TABLE

DIN-
A4
sh: 1