

TD2267



Temperature transmitter with display

TD-250CFED06-A-ZVG/US



EL = installation length



Product characteristics		
Number of inputs and outputs	Number of analogue outputs: 1	
Measuring range	-50...150 °C	-58...302 °F
Communication interface	IO-Link	
Process connection	clamp adapter Ø 6 mm	
Installation length EL [mm]	250	
Application		
Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)	
Media	liquids and gases	
Pressure rating [bar]	160	
Pressure rating [MPa]	16	
Vacuum resistance [mbar]	-1000	
Vacuum resistance [MPa]	-0.1	
Electrical data		
Operating voltage [V]	18...32 DC; ("supply class 2" to cULus)	
Current consumption [mA]	< 50	
Protection class	III	



Temperature transmitter with display

TD-250CFED06-A-ZVG/US

Reverse polarity protection	yes
Power-on delay time [s]	2
Inputs / outputs	
Number of inputs and outputs	Number of analogue outputs: 1
Outputs	
Total number of outputs	1
Output signal	analogue signal; IO-Link; (configurable)
Number of analogue outputs	1
Analogue current output [mA]	4...20
Max. load [Ω]	300
Short-circuit protection	yes
Overload protection	yes
Measuring/setting range	
Measuring range	-50...150 °C -58...302 °F
Factory setting	0...100 °C
Resolution	
Resolution of analogue output [K]	0.04
Resolution of display [K]	0.1
Accuracy / deviations	
Precision analogue output [K]	± 0,3 + (± 0,1 % MS)
Temperature coefficient [% of the span / 10 K]	0,1; (in case of deviation from the reference condition 25 °C)
Response times	
Dynamic response T05 / T09 [s]	1 / 3
Interfaces	
Communication interface	IO-Link
Transmission type	COM2 (38,4 kBaud)
IO-Link revision	1.1
Operating conditions	
Ambient temperature [°C]	-25...80
Storage temperature [°C]	-40...100
Protection	IP 67; IP 68; IP 69K
Tests / approvals	
EMC	DIN EN 61000-6-2
	DIN EN 61000-6-3
Shock resistance	DIN IEC 68-2-27
Vibration resistance	DIN IEC 68-2-6
MTTF [years]	407
Note on approval	factory certificate available as download at www.factory-certificate.ifm
UL approval	UL Approval no. K001
Mechanical data	
Weight [g]	255.5
Housing	cylindrical

TD2267



Temperature transmitter with display

TD-250CFED06-A-ZVG/US

Dimensions	[mm]	Ø 6 / L = 298
Materials		stainless steel (316L/1.4404); PEI; FKM
Materials (wetted parts)		stainless steel (316L/1.4404) electropolished
Process connection		clamp adapter Ø 6 mm
Surface characteristics Ra/Rz of the wetted parts		Ra: < 0.8
Probe diameter	[mm]	6
Installation length EL	[mm]	250

Displays / operating elements

Display		7-segment LED display, 4-digit
		display unit / status, °C / °F

Remarks

Remarks		MS = set measuring span
		The values for accuracy apply to flowing water.
Pack quantity		1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection

