






1. CENTER CONTACT:
USE CRIMP TOOL: 360X10329X
WITH TOOL INSERT: 360X11059X
SELECTOR SETTING: 5 (FOR AWG26 CENTER CONDUCTOR OF CABLE)
2. CRIMP FERRULE:
USE CRIMP TOOL: 360X10519X
WITH TOOL INSERT: 360X11019X
INSERT CAVITY B: HEX 3.25/.128



Part no.	Finish Pos.1	Finish Pos.2	Finish Pos.3	Finish Pos.4 + 5 + 7 + 6
132A23019X	GOLD FLASH over NICKEL	GOLD FLASH over NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL
132J23019X	min. 50µin HARD GOLD over min. 50µin NICKEL	min. 30 min HARD GOLD over min. 50 min NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.

DO NOT ALTER CAD DRAWING BY HAND

a	Original		
rev.	description	date	name



tolerance		 dim. in mm
drawn	19.03.14	Henneboel
ppd.	20.03.14	Koch
norm		
-old		

scale:	5:1	
material:	COPPER ALLOY (Pos. 1-7)	
title:		
COAXIAL CONTACT SOCKET 90°, 50 Ohm inner + outer conductor for crimp termination for cable RG 174/U, 188A/U, 316/U		
dwg no:	13K2A050A	DIN- A3
		sh: 1
part no:	SEE TABLE	