



4

3

2

1

used for: D-SUB COMBINATION



Directive 2002/95/EC
„RoHS“
Compliant

NOTES:

1. MATERIAL: COPPER ALLOY
2. PLATING:
ITEM 1: min. 30µ" HARD GOLD OVER min. 50µ" NICKEL
ITEM 2: TIN PLATED
ITEM 3: NICKEL PLATED
3. PCB-THICKNESS: min. 1.6mm
Ø PCB-HOLE: 3.02mm min. / 3.20mm max.

APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance ISO 2768-m		 dim. in mm
				2003	date	name
				drawn	30.10.	Lehmenkühler
				appd.	30.10.	Mickenbecker
				norm		
				d-old		
						
rev.	description	date	name			

scale:	5:1	
material:	SEE NOTES	
title:	HIGH POWER CONTACT FEMALE PRESSFIT VERSION 30A D-SUB COMBINATION	
dwg no:	AutoCAD 2000	DIN-A
	13K1A979	4
		sh: 1/1
part no:	132C19019X	

4

3

2

1