





used for: D-SUB HD

POS.	A -0.76	B +0.25	C	D -0.3	Part NO.
26	39.52	25.12	33.30 ± 0.15	6.12	163A17779X
44	53.42	38.84	47.04 ± 0.13	5.99	163A17789X
62	69.70	55.30	63.50 ± 0.13	5.99	163A17799X



NOTES:

- METALSHELLS: STEEL; min. 320µin TIN
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 8µin HARD GOLD over min. 50µin NICKEL
- METAL BRACKET: DIE-CASTING; min. 320µin TIN over 80µin NICKEL
- THREADED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- PCB-SNAP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: $\Phi 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
- FIXING-PLATE: PBT GF UL 94 V-0, BLACK
- P.C.B. HOLE DRILLINGS ON SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: **PART-NO. CONEC ABC**

RoHS compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL
CUSTOMER APPROVAL DATE:
NAME: TITLE:
COMPANY NAME:
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Original		


tolerance	dim. in mm
2006	date
drawn	27.01.
appd.	27.01.
norm	DIN 41652
d-old	

CONEC


scale:	2:1 (5:1)
material:	SEE NOTES
title:	D-SUB HD MALE 90° 26-62pos. 0.350inch threaded insert, metal bracket, fixing-plate, clip
dwg no:	AutoCAD 2004
part no:	SEE TABLE

DIN-A
3
sh:1/2


used for: D-SUB HD



26pos.



44pos.



62pos.

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Original		

tolerance		dim. in mm	name
2006	date		
drawn	27.01.	Lehmenkühler	
appd.	27.01.	Mickenbecker	
norm			
d-old			

CONEC

scale:	2:1
material:	SEE SHEET 1
title:	P.C.B. HOLE DRILLINGS D-SUB HD MALE 90° 26-62pos. 0.350inch threaded insert, metal bracket, fixing-plate, clip
dwg no:	AutoCAD 2004 DIN-A
	16K1A1722 3
part no:	SEE SHEET 1
	sh:2/2