







NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY; PLATING (SEE PART NO):
☐ PLEASE ADD A for GOLD FLASH over NICKEL (PREFERRED TYPE)
☐ PLEASE ADD B for 20µin HARD GOLD over min. 50µin NICKEL
☐ PLEASE ADD C for 30µin HARD GOLD over min. 50µin NICKEL
- METAL BRACKETS:
 ZINC DIE CAST; 300µin COPPER/40-120µin NICKEL/120-200µin TIN
- THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- FIXING PLATE: PBT GF UL 94 V-0, BLACK
- P.C.B. HOLE DRILLINGS ON SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 164□15659X CONEC ABC (see note 3)


RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale: 2:1	
								material: SEE NOTES	
					date	name	title: D-SUB DUAL PORT 15.88mm 15pos. FEMALE / 15pos. MALE threaded insert, metal bracket, fixing plate		
					drawn 29.02.2016	Unkrüer			
					appd. 29.02.2016	Lehmenkühler	dwg no: 16K1A3755 part no: 164□15659X (see note 3)		
					norm				
					d-old		CONEC®		
	a	Original							
	rev.	description	date	name					

CONEC®

P.C.B. HOLE DRILLINGS

(P.C.B. TOP SIDE)



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 3:1
								material: SEE SHEET 1
					date	name	title: P.C.B. HOLE DRILLINGS D-SUB DUAL PORT 15.88mm 15pos. FEMALE / 15pos. MALE	
					drawn 29.02.2016	Unkrüer		
					appd. 29.02.2016	Lehmenkühler		
					norm			
					d-old			
	a	Original					dwg no:	DIN-A3
	rev.	description	date	name			16K1A3755	sh: 2/2
							part no: SEE SHEET 1	