








NOTES:

1. METAL SHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 8µm HARD GOLD over min. 50µm NICKEL
4. METAL BRACKET: STEEL; min. 320µm TIN over 80µm NICKEL
5. THREADED LOCK: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
6. FIXING PLATE: PBT GF UL 94 V-0, BLACK
7. PCB-SNAP: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
PCB-HOLE: $\varnothing 3,1 \pm 0,1$ mm; PCB-THICKNESS: 1,6 mm
8. MAXIMUM TORQUE VALUE FOR THREAD: 6 in. LB
9. CONNECTOR IS PART MARKED: 164A19759X CONEC ABC

Directive 2002/95/EC
"RoHS"
Compliant



APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

finish:			
SEE NOTES			
rev.	description	date	name
a	Origin		

tolerance		 dim. in mm
	date	name
drawn	25.01.07	Lehmenkühler
appd.	25.01.07	Mickenbecker
norm	DIN 41652	
d-old		
		

scale:	2:1		
material:	SEE NOTES		
title: D-SUB DUAL PORT 15.88mm 9pos. FEMALE / 9pos. FEMALE with threaded lock and snap			
dwg no:		Inventor	DIN- A3
16K1A1970		sh: 1	
part no:		164A19759X	