






1. METAL SHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY; PLATING (SEE PART NO):
 - ☐ PLEASE ADD A for GOLD FLASH over NICKEL (PREFERRED TYPE)
 - ☐ PLEASE ADD B for 20µin HARD GOLD over min. 50µin NICKEL
 - ☐ PLEASE ADD C for 30µin HARD GOLD over min. 50µin NICKEL
4. METAL BRACKETS:
 - ZINC DIE CAST; 300µin COPPER/40-120µin NICKEL/120-200µin TIN
5. THREADED LOCKS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. FIXING PLATE: PBT GF UL 94 V-0, BLACK
7. PCB-SNAP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- ☐ PCB-HOLE: Ø3,1±0,1mm; PCB-THICKNESS 1,6mm
8. P.C.B. HOLE DRILLINGS ON SHEET 2
9. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
10. CONNECTOR IS PART MARKET: 164019809X CONEC ABC (see note 3)

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 2:1	
					material:			SEE NOTES	
					date	name	title: D-SUB DUAL PORT 15.88mm 15pos. FEMALE / 15pos. MALE threaded lock, metal bracket, fixing plate and clip		
					drawn	16.01.13 Henneboel			
					appd.	17.01.13 Fischer			
					norm				
					d-old 16K1A1762		dwg no: 16K1A3171		DIN-A3 sh: 1/2
	4 x b	Ã4610	16.01.2013	K.H.					
	a	Original							
	rev.	description	date	name			part no: (b) 164□19809X (see note 3)		

Directive 2002/95/EC RoHS compliant

P.C.B. HOLE DRILLINGS

(P.C.B. TOP SIDE)



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 3:1					
							material: SEE SHEET 1					
									date	name	title: P.C.B. HOLE DRILLINGS D-SUB DUAL PORT 15.88mm 15pos. FEMALE / 15pos. MALE	
								drawn	16.01.13	Henneboel		
								appd.	17.01.13	Fischer		
				norm				dwg no:	DIN-A3 sh: 2/2			
				d-old		16K1A1762						
	a	Original						16K1A3171				
rev.	description	date	name					part no: SEE SHEET 1				