




Pos.	A	B	C	D	E	ϕF	$G^{+0.6}$	H	Part NO. Bulk package	Part NO. Single package
9	31.7	25.0	30.0	32.7	15.0	5.0	9.0	9.0	165X17409X	165X17409XE
15	40.0	33.3	32.0	34.7	15.0	5.0	9.0	9.0	165X17419X	165X17419XE
25	53.7	47.0	35.0	37.7	15.0	7.0	12.2	10.0	165X17429X	165X17429XE
37	70.2	63.5	41.0	43.7	15.0	7.0	13.5	11.0	165X17439X	165X17439XE
50	67.8	61.1	41.0	43.7	17.7	9.3	15.3	12.7	165X17449X	165X17449XE

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

NOTES:

1. CASE: ZINC DIECAST; NICKEL PLATED
2. SHORT SCREW: STEEL; NICKEL PLATED
3. CABLE BUSHING: TPE
4. CABLE STRAIN RELIEF: STEEL; NICKEL PLATED
5. ATTENUATION FACTOR >60dB BETWEEN 300 MHz AND 900 MHz

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND	tolerance				scale: 1:1
					material: SEE NOTES
	2005 date name				title: METAL HOOD 9-50pos. EMI / RFI SHIELDING with straight cable exit and short screws
	drawn 07.02. Lehmenkühler				
	appd. 07.02. Kühle				
1 x d	Ä7543	25.10.2018	JLE	norm	dwg no: AutoCAD 2004 DIN-A 4
1 x c	Ä3466	20.10.2009	Lehmen.	d-old	
1 x b	Ä2180	09.03.2005	Lehmen.		part no: SEE TABLE
a	Origin				
rev.	description	date	name		