


# UGT200

## Ultrasonic sensor

UGC00300EOKG/US



1 LEDs



### Product characteristics

|                    |                                                    |
|--------------------|----------------------------------------------------|
| Electrical design  | PNP                                                |
| Output function    | normally open / normally closed; (parameterisable) |
| Sensing range [mm] | 40...300; (Target: 200 x 200 mm)                   |
| Housing            | threaded type                                      |
| Dimensions [mm]    | M18 x 1 / L = 60.5                                 |

### Electrical data

|                             |                                         |
|-----------------------------|-----------------------------------------|
| Operating voltage [V]       | 10...30 DC; ("supply class 2" to cULus) |
| Current consumption [mA]    | < 35                                    |
| Protection class            | III                                     |
| Reverse polarity protection | yes                                     |
| Power-on delay time [s]     | < 0.3                                   |
| Converter frequency [kHz]   | 300                                     |

### Inputs / outputs

|                              |                              |
|------------------------------|------------------------------|
| Number of inputs and outputs | Number of digital outputs: 1 |
|------------------------------|------------------------------|

### Inputs

|                       |    |
|-----------------------|----|
| Synchronisation input | no |
| Multiplex input       | no |

### Outputs

|                                                      |                                                    |
|------------------------------------------------------|----------------------------------------------------|
| Total number of outputs                              | 1                                                  |
| Electrical design                                    | PNP                                                |
| Number of digital outputs                            | 1                                                  |
| Output function                                      | normally open / normally closed; (parameterisable) |
| Max. voltage drop switching output DC [V]            | 2.2                                                |
| Permanent current rating of switching output DC [mA] | 100                                                |
| Switching frequency DC [Hz]                          | 8                                                  |
| Short-circuit protection                             | yes                                                |
| Overload protection                                  | yes                                                |

# UGT200



## Ultrasonic sensor

UGC00300EOKG/US

| Detection zone                                  |                           |                                                                                              |
|-------------------------------------------------|---------------------------|----------------------------------------------------------------------------------------------|
| Sensing range                                   | [mm]                      | 40...300; (Target: 200 x 200 mm)                                                             |
| Blind zone                                      | [mm]                      | 40                                                                                           |
| Angle of aperture cylindrical                   | [°]                       | 15; (±2)                                                                                     |
| Max. deviation from the 90° angle sensor/object | [°]                       | ± 4                                                                                          |
| Accuracy / deviations                           |                           |                                                                                              |
| Temperature compensation                        |                           | yes                                                                                          |
| Hysteresis                                      | [%]                       | < 1                                                                                          |
| Switch point drift                              | [%]                       | -5...5                                                                                       |
| Repeatability                                   |                           | 1 %                                                                                          |
| Resolution                                      | [mm]                      | 2                                                                                            |
| Notes on the accuracy / deviation               |                           | The indicated values are reached after a warm-up time of min. 20 minutes                     |
| Operating conditions                            |                           |                                                                                              |
| Ambient temperature                             | [°C]                      | -20...70                                                                                     |
| Storage temperature                             | [°C]                      | -30...80                                                                                     |
| Protection                                      |                           | IP 67                                                                                        |
| Tests / approvals                               |                           |                                                                                              |
| EMC                                             | EN 61000-4-2 ESD          | 4 kV CD / 8 kV AD                                                                            |
|                                                 | EN 61000-4-3 HF radiated  | 3 V/m                                                                                        |
|                                                 | EN 61000-4-4 Burst        | 2 kV                                                                                         |
|                                                 | EN 61000-4-6 HF conducted | 3 V                                                                                          |
|                                                 | EN 55011                  | Class A                                                                                      |
| Vibration resistance                            | EN 60068-2-6 Fc           | (10-55) Hz 1 mm amplitude, oscillation period 5 min., 30 min. per axis at resonance or 55 Hz |
| Shock resistance                                | EN 60068-2-27 Ea          | 30 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes              |
| MTTF                                            | [years]                   | 202                                                                                          |
| UL approval                                     | Ta                        | -20...70 °C                                                                                  |
|                                                 | power supply              | Class 2                                                                                      |
|                                                 | File number UL            | E174191                                                                                      |
| Mechanical data                                 |                           |                                                                                              |
| Weight                                          | [g]                       | 56                                                                                           |
| Housing                                         |                           | threaded type                                                                                |
| Dimensions                                      | [mm]                      | M18 x 1 / L = 60.5                                                                           |
| Thread designation                              |                           | M18 x 1                                                                                      |
| Materials                                       |                           | PBT; PA; epoxy glass ceramics                                                                |
| Tightening torque                               | [Nm]                      | 1                                                                                            |
| Displays / operating elements                   |                           |                                                                                              |
| Display                                         | switching status          | 1 x LED, yellow                                                                              |
|                                                 | echo                      | 1 x LED, green                                                                               |
| Accessories                                     |                           |                                                                                              |
| Items supplied                                  |                           | lock nuts: 2, plastics                                                                       |
|                                                 |                           | rubber washers: 2                                                                            |

# UGT200



## Ultrasonic sensor

UGC00300EOKG/US

### Remarks


|               |                                                       |
|---------------|-------------------------------------------------------|
| Remarks       | operating voltage "supply class 2" according to cULus |
| Pack quantity | 1 pcs.                                                |

### Electrical connection

Connector: 1 x M12; coding: A



### Connection



2: Teach



### Diagrams and graphs



- 1: distance
- 2: Detection zone
- 3: switch-on/switch-off graph
- 4: Target 100 x 100 mm
- 5: 50% of the target in the detection zone
- 6: switch point