




Notes:

1. Electrical Specifications:

- Meets USB 2.0 Specification
- Contact Resistance: 30 mOhm max.
- Insulation Resistance: 1000 MOhm min. @ 100 VDC
- Current Rating: 1.5 A max. at 25°C
- Working Voltage: 30 V (RMS) max.
- DWV: 500 VAC/60s at sea level
- Operating Temperature: -40°C to +85°C

2. Material and Finish:

- Receptacle Housing and Protective Cover: Polyester, UL94 V-0, Color: Black
- © or ABS, Nickel Plated, UL94 V-0
- Panel Nut: Brass, Finish: Nickel Plated
- Panel and Cover Gasket: Silicon, Color: White
- Tether: Polycarbonate, Color: Black
- USB Adaptor Insulator: PBT, UL94 V-0, Black
- USB Adaptor Metal Shell: Copper Alloy, Nickel Plated
- USB Adaptor Overmold material: PBT UL94 V-0, Color: Black
- USB Contacts: Copper Alloy, Finish: 30 u" Gold min. over Nickel

3. Connector can be mounted to a maximum panel thickness of 3.2 mm.

4. IP67 rated when covered or fully mated with the appropriated mating connector

RoHS compliant

Version	Part Number
Black Plastic Version	17-210141
Metallized Plastic Version	17-210181

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY. AND MAY NOT BE REPRODUCED TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION	Customer:				Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°			Scale:		Dim. in mm	
	Name		Title		Approval Date			Autodesk Inventor		Material: See Notes	
									Receptacle + Cover Assembly Kit		
							2012 Date Name		Both Sides Bayonet Receptacle Housing		
							Draw. Sept. 28 Vincent Ke		with USB Type A F/F Adaptor		
	1 x e		Ä21-0426		03.11.2021 Bub		Appd. Sept. 28 J. Chaudry				
	d		1 x d		May/05/2014 Vincent Ke		Norm				
	c		3 x c		Jan/18/2013 Vincent Ke		D-old				
	b		1 x b		Oct/17/2012 Vincent ke				Drawing No.: 17K1A357		
	a		original						DIN A3		
Rev.		Changes		Date		Name		Part No.: SEE PART NUMBER TABLE		Sheet 1/1	
											