








Notes:

1. Electrical Specifications:

- Meets USB 2.0 Specification
- Contact Resistance: 30 mOhm max.
- Insulation Resistance: 1000 MOhm min. @ 100 VDC
- Current Rating: 1.5 A max. at 25°C
- Working Voltage: 30 V (RMS) max.
- DWV: 500 VAC/60s at sea level
- Operating Temperature: -40°C to +85°C

2. Material and Finish:

- Receptacle Housing and Dust Cap: Polyester, UL94 V-0 (Black), UL94 V-0
- Panel Nut: Brass, Finish: Nickel Plated
- Panel and Cover Gasket: Silicon, Color: White
- Ball Chain Assembly: Copper Alloy and Stainless Steel, Nickel Plated
- M2 Self Taping Screw: Stainless Steel
- USB Insulator: PBT, UL94 V-0, Black
- USB Metal Shell: SPCC, Nickel Plated
- USB Overmold material: PBT UL94 V-0, Color: Black
- USB Contacts: Copper Alloy, Finish: 30 u" Gold min. over Nickel
- PCB: FR-4, UL94 V-0, Color: Green

3. Maximum panel thickness of 3.2 mm

4. Recommended Mounting Panel Nut torque is 20 to 25 lb-inch

Pin to typical USB Cable Wiring Assignment

Type A F	PCB	Signal Name	USB Cable
Pin1	P1	VBUS	Red
Pin2	P2	D-	White
Pin3	P3	D+	Green
Pin4	P4	GND	Black
Shell	GND	GND	Drain Wire

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION	DOT NOT ALTER CAD DRAWING BY HAND	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°		Scale:		Dim. in mm		
		Name		Title			Approval Date	Material: See Notes			
								Title: Potted IP67 Dual Port USB Receptacle + Dust Cap Assembly Kit with dual USB 2.0 Type A F to PCB			
								Drawing No.: 17K1A636			
								Part No.: 17-210581			
								DIN A3			
								Sheet 1/1			