









P.C.B.HOLE DRILLINGS



NOTES:

1. METALSHIELDS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. COAXIAL CONTACTS 50 OHM: COPPER ALLOY
PLATING INNER CONDUCTOR: 50µin HARD GOLD over min. 50µin NICKEL
PLATING OUTER CONDUCTOR: 30µin HARD GOLD over min. 50µin NICKEL
4. METEL BRACKET: ZINC DIE CAST; 300µin COPPER/ 40-120µin NICKEL/ 120-200µin TIN
5. THREADED INSERT: COPPER ALLOY; min 200µin TIN over 80µin NICKEL
6. PCB-SNAP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: $\varnothing 3,1 \pm 0,1$; PCB THICKNESS 1,6mm
7. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
8. CONNECTOR IS PART MARKED: 3003W3PXX78N40X CONEC ABC

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance			scale: 2:1(5:1)	
				date			material: SEE NOTES	
				name			title:	
				drawn: 27.08.2007 Sonnenberg			D-SUB COMBINATION MALE	
appd. 27.08.2007 Mickenbecker		norm		3W3P		with threaded insert ,metal bracket and snap		
d-old		a		dwg no:		Inventor 10		
rev. description		date		name		13K1A2207		
DO NOT ALTER CAD DRAWING BY HAND		CONEC		part no:		3003W3PXX78N40X		
						DIN-A3 sh: 1		