


RoHS Compliant

| Rev.                                           | SIGN | DATE       | DESCRIPTION       | APPROVER |
|------------------------------------------------|------|------------|-------------------|----------|
| B                                              | —    | 2024.05.12 | The first release | Guoxue   |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |      |            |                   |          |

Technical Specification:

1. Material: Copper alloy,Matte Tin Plated.
2. Current: 40A.
3. Torque: 10 lbf.in.
- 4.Mark "▲" is the Critical dimension.



|      |           |                                |      |
|------|-----------|--------------------------------|------|
| ⑥    | Spacer    | Steel , Matte Tin Plated       | 1PCS |
| ①    | terminal  | Copper alloy, Matte Tin Plated | 1PCS |
| ITEM | PART NAME | DESCRIPTION                    | Q`ty |

|                                       |         |                               |                      |                                                                                                                                                                                                                                    |          |             |            |
|---------------------------------------|---------|-------------------------------|----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|-------------|------------|
| <div>Amphenol</div> <div>ANYTEK</div> |         |                               |                      | <div>CUSTOMER COPY</div> <div>ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES<br/>IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUTWRITTEN AUTHORITY<br/>FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD</div> |          |             |            |
| TITLE                                 |         | AMT43015DB Conductive Bracket |                      |                                                                                                                                                                                                                                    |          |             |            |
| PART NO.                              |         | AMT0430015DB0000G             |                      | DWG NO.                                                                                                                                                                                                                            | 8AMT0007 |             |            |
| APPROVED                              | CHECKED | DESIGNED                      | DRAWN                | CUST NO.                                                                                                                                                                                                                           |          | Tolerance   |            |
|                                       |         | Guoxue<br>2024.05.12          | Guoxue<br>2024.05.12 |                                                                                                                                               |          | UNIT: mm    | >30 ±0.60  |
|                                       |         |                               |                      |                                                                                                                                                                                                                                    |          | SCALE: NONE | 6-30 ±0.40 |
|                                       |         |                               |                      |                                                                                                                                                                                                                                    |          | REV.: B     | 0-6 ±0.30  |
|                                       |         |                               |                      | SHEET: 01/01                                                                                                                                                                                                                       |          |             | ANGLES ±1° |