




NOTES:

1. METALSHELLS: STEEL; min. 320µ" TIN
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. THREADED INSERT: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
4. COLLAR: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
5. MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
6. = CRITICAL DIMENSION
7. CONNECTOR IS PART MARKED: PART NO: CONEC Y/WW

Directive 2002/95/EC
RoHS
Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance				scale: 2:1							
								material: SEE NOTES							
								2002		date	name	title: D-SUB COMBINATION MALE 7W2P CRIMP STYLE			
								drawn		06.08.	Schmidt				
								appd.		06.08.	Mickenbecker				
								norm							
								d-old							
												dwg no:		AutoCAD 2000	DIN-A
												13K1A667		3	
												sh: 1/1			
rev.	description	date	name	part no: 3007W2PXX99A30X											