





used for: D-SUB COMBINATION CRIMP



PART NO.
3007W2SXX99A30X
CFLT7W2S7-K121

Directive 2002/95/EC
RoHS
Compliant

NOTES:

1. METAL SHELLS: STEEL; min. 320µ" TIN
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. THREADED INSERT: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
4. COLLAR: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
5. MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
6. = CRITICAL DIMENSION
7. CONNECTOR IS PART MARKED: PART NO: CONEC Y/WW

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance		
2002	date	name
drawn	06.08.	Schmidt
appd.	06.08.	Mickenbecker
norm		
d-old		
CONEC®		

scale:		2:1	
material:		SEE NOTES	
title: D-SUB COMBINATION FEMALE CRIMP STYLE 7W2S			
dwg no:		AutoCAD 2000	DIN-A
13K1A666			3
			sh: 1/1
part no:		SEE TABLE	