

REV	SIGN	DATE	DESCRIPTION	APPROVER
D	△	01/27'07	The soldering temperature from 245°to 250°	Aaron
E	△	10/09'12	Update the drawing	Da cheng
F	△	04/11'13	Update the drawing	Da cheng
G	△	08/26'14	Update the drawing	Airy min
H	△	03/28'17	Change the dimension from3.8 to 3.5	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

△ Material

- Item ① Terminal body (Contact pin): Brass, Bright Tin plated over Nickel plated
- Item ② Spring clamp: Stainless steel
- Item ③ Terminal Cover: Thermoplastic (UL94V-0)
- Item ④ Terminal Body: Thermoplastic (UL94V-0)
- Item ⑤ Pad board: Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Pull force:
- Screw:
- △ Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- △ ● Operating temperature: -40°C to +115°C
- △△ ● Soldering temperature: 260°C±5°C/5 Sec
- △ ● Safety Approval:
- △ ● Critical dimension: △ 

HG xx 20 x 0 xxxx G

02 2 CONTACTS
03 3 CONTACTS
... ...
16 16 CONTACTS

△△ Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors

000 0 Standard @ Logo
000 A Standard ANY Logo
Any special item by customer request, please contact sales department.






RoHS compliant (lead<4%) △
In copper Alloy

△ Dimension

DIM A	(N-1)×7.5+5.9
DIM B	(N-1)×7.5

△ N=Number of poles

POLES	DIM B	DIM A
2p-4p	±0.15	±0.20
5p-8p	±0.20	±0.25
9p-12p	±0.25	±0.30
13p-16p	±0.30	±0.40




PCB LAYOUT
△ Bottom view

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HG 7.5mm Series						
PART NO.	HGxx20x0xxxxG			DWG NO.	8HG0201		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Chen Bo 03/28-17	Airy min 2015.07.21		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					SHEET: 01/01		REV: H
							X° ±1°