







DIMENSION

Dim A	NX3.50+1.40
Dim B	(N-1)X3.50

N=Number of contacts

Poles	Tolerance
1p-6p	±0.10
7p-12p	±0.20
13p-18p	±0.30
19p-24p	±0.40



Ver	SIGN	DATE	DESCRIPTION	APPROVER
C	△	04/05'13	change the structure & update the drawing	Da cheng
D	△	10/17'13	Add is cULus	Da cheng
E	△	02/27'17	Add "TUV" Mark	Eddie
F	△	2017-11-27	"TUV" Current rating:24A change 17.5A	Zhihua
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Material:

- Item 1 Terminal housing : Thermoplastic (UL 94V-0)
- Item 2 Spring clamp: Stainless steel
- Item 3 Solder pin : Brass ,Tin plated
- Item 4 Terminal cover : Thermoplastic (UL 94V-0)

Electrical	cULus	TUV
● Voltage rating:	300VAC	130 V
● Current rating:	10A	17.5A △
● Wire range:		0.2-1.5mm ²
● Solid wire(AWG):	16-24	
● Stranded wire(AWG):	16-24	
● Wire strip length:	9-10mm	
● Withstanding Voltage:	1.6KV	
● Operating temperature:	-40°C to +115°C	
△ Soldering temperature:	260°C±5°C/5 Sec	

- △ Safety Approval:
- Critical dimension:



NJ xx 21 x 0 xxxx G

No. of poles

01 1 CONTACTS

02 2 CONTACTS

03 3 CONTACTS

... ..

24 24 CONTACTS

△ Color

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7004/P)

9 White(RAL1102)

C Multiple colors

△ RoHs compliant
(lead<4%)
In copper Alloy

0000:"@ "Logo (Standard)

000A:"ANYTEK"Logo

Any special item by
customer request,
please contact sales
department.

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		NJ- 3.5 Series 1P-24P Horizontal (180D wire inlet)				
PART NO.	NJxx21x0xxxxG			DWG NO.	8NJ0001	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Zhihua 2017.11.27	Zhihua 2017.11.27		Tolerance	
					X. ±0.50	
					X.X ±0.30	
					X.XX ±0.10	
				SHEET: 01/01	REV.: F	
					X° ±1°	