






PCB hole drillings
(PCB top side)/
Leiterplattenbohrbild
(Leiterplatten Oberseite)



			 dim. in mm		D-SUB Combination Female 90° 25W3S with threaded insert, metal bracket and PCB snap		
general tolerance/ <i>Allgemeintoleranz:</i>	0	± 0,50 mm	Date/ <i>datum</i>	Name		<i>D-SUB Combination Buchsenleiste 90° 25W3S mit Gewindeeinsatz, Metallwinkel und PCB Clip</i>	
	0,0	± 0,25 mm	drawn/ <i>gez.</i>	21.12.2022 Lehmenkühler			
	0,00	± 0,10 mm	appd./ <i>gepr.</i>	22.12.2022 Unkrüer			
		scale/ <i>Maßstab:</i>			dwg no / Z.-nr.: 13K1A6429		
Index: a Original		2:1			DIN-A3		
RoHS compliant/ <i>konform</i>					2 / 2		