



RoHS Compliant





VIEW A



N = Number of poles
Dim.L=Nx5.0
Dim.B=(N-1)x5.0

Poles	Tol.	Dim.L
2-6p	±0.15	
7-12p	±0.20	
13-18p	±0.30	
19-24p	±0.40	



Material

- Item ① Terminal body(metal housing): Brass(CuZn),Tin plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Wire guard: Stainless steel
- Item ④ Insulator (housing): Thermoplastic (UL94V-0)

- Electrical cULus / VDE
- Voltage rating: 300VAC 250VAC
 - Current rating: 16A 17.5A
 - Wire range: 0.5-1.5mm²
 - Solid wire(AWG): 14-22
 - Stranded wire(AWG): 14-22
 - Torque: 2.6Lb-In 0.4N.m
 - Screw: M2.6
 - Wire strip length: 5-6mm
 - Withstanding Voltage: 1.6KV 2KV
 - Operating temperature: -40°C to +115°C
 - Wave Soldering temperature: 260°C±5°C/5 Sec
 - SAFETY APPROVAL: cULus VDE
 - Critical dimension: ▲
 - Reference dimension: (×)The dimensions of pitch are just for reference, take the actual assembly result as a judgment when inserting the terminal block into the PCB hole.

TC xx 0 3 x x xxx G RoHS compliant (lead<4%) in copper Alloy

POLES	Color	DIM A Length	A50 0 @ Mark
02 02 POLES	0 Black (RAL9005)	0 4.4mm	A50 A ANY Mark
03 03 POLES	2 Red (RAL3001/D)	1 3.8mm	Any special item by customer request, please contact sales department.
...	3 Orange(RAL2011/P)	2 3.5mm	
24 24 POLES	4 Yellow(RAL1018/A)	3 2.9mm	
	5 Green(RAL6018/T)		
	6 Blue (RAL5015/A)		
	8 Grey(RAL7035/D)		
	C Green(RAL6018/U)		

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TC-5.0mm Solid Block type series (2p-24p) "-"				DWG NO. 8TC0102	
PART NO.	TCxx03xxxxxxG				DWG NO. 8TC0102	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
		Guoxue 2023.09.15	Guoxue 2023.09.15		X. ±0.50	
					X.X ±0.30	
					X.XX ±0.10	
					X° ±1°	
					SHEET: 01/01	
					REV.: L	