




used for: D-SUB

NOTES:

- (b) 1. METALSHELLS: STEEL; NICKEL PLATED
2. INSULATORS: PA UL 94 V-0; BLACK
3. PLATING: GOLD FLASH over NICKEL
4. PCB-SNAPS: COPPER ALLOY; TIN PLATED
PCB-HOLE: $\varnothing 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
5. PCB-BOARD DRILLINGS ON DRAWING No.16K111UA
6. CONNECTOR IS PART MARKED:

PART-NO. CONEC ABC



POS.	A -0.76	B -0.25	C	PART-NO.
9	31.19	16.46	25.00 ± 0.12 -0.13	302A11339X
15	39.52	24.79	33.30 ± 0.15 -0.1	302A11349X
25	53.42	38.50	47.04 ± 0.13	302A11359X
37	69.70	54.96	63.50 ± 0.13	302A11369X

RoHS Compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

1 x b	Ä 5865	29.10.2015	Unkriert
a	Original		
rev.	description	date	name

tolerance			dim. in mm
2002	date		
drawn	24.04.		name
appd.	24.04		E. Mickenbeker
norm	DIN 41652		
d-old			

CONEC

scale:	2:1
material:	SEE NOTES
title:	
D-SUB FEMALE 90° 0.318inch 9-37pos. with threaded insert and clip	
dwg no:	DIN-A 3 sh: 1/1
part no:	SEE TABLE