






CONTACT PLATING	PART-NO.
SIGNAL CONTACTS GOLD FLASH over NICKEL	3H15W4PAM62A10X
HIGH POWER CONTACTS PLATING MATING AREA: GOLD FLASH over NICKEL PLATING TERMINATION SIDE: GOLD FLASH over NICKEL	
SIGNAL CONTACTS 30µin HARD GOLD over 50µin NICKEL	
HIGH POWER CONTACTS PLATING MATING AREA: 30µin HARD GOLD over min. 50µin NICKEL PLATING TERMINATION SIDE: GOLD FLASH over NICKEL	3H15W4PCM42A10X



NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: SEE TABLE
SOLDER CUP ACCEPTS CABLE AWG 22
- HIGH POWER CONTACTS 20A: COPPER ALLOY
PLATING: SEE TABLE
SOLDER CUP ACCEPTS CABLE AWG 12-14
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND					tolerance	 dim. in mm	scale: 2:1 (5:1)
							material: SEE NOTES
					date	name	title: D-SUB HD COMBINATION MALE 15W4P SOLDER CUP
					drawn 25.05.10	Lehmenkühler	
					appd. 25.05.10	Koch	
					norm		
					d-old		dwg no: DIN-A3 13K1A3218 sh: 1
	a	Origin					
	rev.	description	date	name			
							part no: SEE TABLE