





N = Number of contacts

DIMENSION

A	NX3.5
B	(N-1)X3.5

Poles	Tolerance
2P-8P	±0.10
9P-16P	±0.20
17P-24P	±0.30

	DATE	DESCRIPTION	APPROVER
△	8/07'06	Added VDE standard	梁仁松
△	12/02'08	With flange screw changed from“-“slot type to“+/-“slot type	Jacke
△	12/02'08	The temperature changed from -30°C, +105°C to -40°C, +115°C	Jacke
△	12/10'08	The dimension design changed from 19.1mm to 19.3mm	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Terminal body(metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating “-“ slot type
- Wire guard: PhBz Tin plated
- △● With flange screw: Steel Zinc plating M2.5 “+/-“ slot type
- Insulator (housing): Thermoplastic (UL94V-0)

△Electrical cULus/VDE

- Voltage rating: 300VAC/300VAC
- Current rating: 8A/10A
- Wire range: 1.5MM²
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Torque(Lb-In): 1.7LB-IN / 0.2NM
- Screw: M2
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV /2.5KV
- △● Operating temperature: -40°C to +115°C
- Safety approval: cULus VDE

TS xx 1 1 x D xxxx G

No. OF POLES
02: 2 POLES
:
:
24: 24 POLES

COLOR


0: BLACK
5: GREEN
6: BLUE
8: GREY
0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request, please contact sales department.

RoHS pb<40 , 000ppm

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TS-3.5mm Series With flange (for latch on back side)							
PART NO.		TSxx11xDxxxxG			DWG NO.	8TS0204			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
			Jacke 2008.12.10	Jacke 2008.12.02			UNIT: mm	X.	±0.50
							SCALE: NONE	X.X	±0.30
					SHEET: 01/01		REV.: G	X.XX	±0.10
								X°	±1°