

24: 24 POLES



Color

- 0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)


→ G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo

000A: "ANYTEK" Mark
0091: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.



SECTION P-P



N = Number of poles

Dim A	$N \times 5.08 + 0.5$
Dim B	$(N-1) \times 5.08$
Dim C	$N \times 5.08$

Poles	Dim A/B/C	TOL
2-6p	±0.15	±0.15
7-12p	±0.20	±0.20
13-18p	±0.30	±0.30
19-24p	±0.40	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	11.01'05	Standard spec is changed.	Marivn
△	8/07'06	Added VDE and TUV standard	梁仁松
△	12/02'08	With flange screw changed from“-“slot type to“+/-“slot type	Jacke
△	12/02'08	The temperature changed from -30℃, +105℃ to-40℃,+115℃	Jacke
△	2010.03.12	Add the 2p mark	Jacke
△	2010.08.16	The design is changed	Chen Bo
△	2010.10.19	The drawing is revised	Chen Bo
△	08/06-20	update the drawing	Chen Bo


THIS IS CAD DRAWING. DO NOT REVISE MANUALLY!!!!

Material

- Item ④ Clamp: Brass Ni plating
- Item ⑤ Terminal screw: Steel ,Zinc plating “-” slot type
- Item ⑥ Female contact: PhBz, Bright Tin plated over Nickel plated
- Item ⑦ Terminal up body: Thermoplastic (UL94V-0)
- Item ⑧ Terminal down body: Thermoplastic (UL94V-0)
- Item ⑨ With flange screw : Steel Zinc plating M2.5 “+/-” slot type

 Electrical cULus/VDE/TUV

- Voltage rating: 300VAC/300VAC/300VAC
- Current rating: 15A/17A/15A
- Wire range: 2.5mm² / 0.34-2.5mm²
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 3.5Lb-In./0.5Nm/0.4Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval: cULus  VDE  TÜV 
- Critical dimension: 



Amphenol **ANYTEK**

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TS-5.08mm Series(W/latching hooks on the back side) With flange					
PART NO.		TSxx51xDxxxxG		DWG NO.		8TS0104	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Chen Bo 08/06-20	Jacke 2010.10.19		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
				SHEET: 01/01	REV.: J		X.XX ±0.10
							X° ±1°